

dedicated KVM switch and rackmount screen technology

User Manual 24" Ultra High Resolution LCD 1920 x 1200



751

Legal Information

First English printing, October 2002

Information in this document has been carefully checked for accuracy; however, no guarantee is given to the correctness of the contents. The information in this document is subject to change without notice. We are not liable for any injury or loss that results from the use of this equipment.

Safety Instructions

Please read all of these instructions carefully before you use the device. Save this manual for future reference.

- Unplug equipment before cleaning. Don't use liquid or spray detergent; use a moist cloth.
- Keep equipment away from excessive humidity and heat. Preferably, keep it in an air-conditioned environment with temperatures not exceeding 40° Celsius (104° Fahrenheit).
- When installing, place the equipment on a sturdy, level surface to prevent it from accidentally falling and causing damage to other equipment or injury to persons nearby.
- When the equipment is in an open position, do not cover, block or in any way obstruct the gap between it and the power supply. Proper air convection is necessary to keep it from overheating.
- Arrange the equipment's power cord in such a way that others won't trip or fall over it.
- If you are using a power cord that didn't ship with the equipment, ensure that it is rated for the voltage and current labeled on the equipment's electrical ratings label. The voltage rating on the cord should be higher than the one listed on the equipment's ratings label.
- Observe all precautions and warnings attached to the equipment.
- If you don't intend on using the equipment for a long time, disconnect it from the power outlet to prevent being damaged by transient over-voltage.
- Keep all liquids away from the equipment to minimize the risk of accidental spillage. Liquid spilled on to the power supply or on other hardware may cause damage, fire or electrical shock.
- Only qualified service personnel should open the chassis. Opening it yourself could damage the equipment and invalidate its warranty.
- If any part of the equipment becomes damaged or stops functioning, have it checked by qualified service personnel.

What the warranty does not cover

- Any product, on which the serial number has been defaced, modified or removed.
- Damage, deterioration or malfunction resulting from:

	Accident, misuse, neglect, fire, water, lightning, or other acts of nature, unauthorized product modification, or
	failure to follow instructions supplied with the product.
	Repair or attempted repair by anyone not authorized by us.
	Any damage of the product due to shipment.
	Removal or installation of the product.
П	Causes external to the product, such as electric power fluctuation or failure

- ☐ Use of supplies or parts not meeting our specifications.
- □ Normal wear and tear.
- ☐ Any other causes which does not relate to a product defect.
- Removal, installation, and set-up service charges.

Regulatory Notices Federal Communications Commission (FCC)

This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to Part 15 of the FCC rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation.

Any changes or modifications made to this equipment may void the user's authority to operate this equipment. This equipment generates, uses, and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications.

However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Re-position or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.

Contents

< Part. 1 >	RM-X24	
1.1 1.2 1.3 1.4	Package Content Structure Diagram & Dimension Installation Connection	P.1 P.1 - 2 P.3 - 4 P.5
< Part. 2 >	Specifications / OSD	
2.1 2.2 2.3 2.4	Product Specifications Keyboard / Mouse Specifications On-screen Display Operation (OSD) Picture In Picture (PIP) / Picture By Picture (PBP)	P.6 - 7 P.8 - 10 P.11 - 12 P.13 - 14
< Part. 3 >	Options	
3.1 3.2 3.3	3G / HD / SD- SDI Broadcast-grade input HDMI DC Power: 24V / 48V / 125V / 250V	P.15 P.16 P.16

< Part. 4 > KVM Integration

P.17

Before Installation

- It is very important to mount the equipment in a suitable cabinet or on a stable surface.
- Make sure the place has a good ventilation, is out of direct sunlight, away from sources of excessive dust, dirt, heat, water, moisture and vibration.

Unpacking

The equipment comes with the standard parts shown in package content. Check and make sure they are included and in good condition. If anything is missing, or damaged, contact the supplier immediately.

How To Clean Your LCD Monitor



Caution :

- To avoid the risk of electric shock, make sure your hands are dry before unplugging your monitor from or plugging your monitor into an electrical outlet.
- When you clean your monitor, do not press down on the LCD screen. Pressing down on the screen can scratch or damage your display. Pressure damage is not covered under warranty.
- Use only cleansers made specifically for cleaning monitors and monitor screens. Cleansers not made to clean monitors and monitor screens can scratch the LCD display or strip off the finish.
- Do not spray any kind of liquid directly onto the screen or case of your monitor. Spraying liquids directly onto the screen or case can cause damage which is not covered under warranty.
- Do not use paper towels or abrasive pads to clean your monitor. Using an abrasive pad or any wood based paper product such as paper towels can scratch your LCD screen.

Cleaning Your Monitor

To clean your LCD safely, please follow these steps:

- ① Disconnect the power cord.
- ② Gently wipe the surface using a clean, dry microfiber cloth. Use as little pressure as possible.

Cleaning Tough Marks and Smudges

To remove tough marks and smudges, please follow these steps:

- ① Disconnect the power cord.
- 2 Spray a small amount of non-abrasive cleanser on a microfiber cloth.
- Caution: Do not spray or apply any liquids directly onto the monitor. Always apply the solution to your microfiber cloth first, not directly on the parts you are cleaning.
- Gently wipe the surface. Use as little pressure as possible.
- Wait until your monitor is completely dry before plugging it in and powering it up.

< Part 1 >

< 1.1 > Package Content




RM-X24 unit X1

- CX-6 6ft DVI-D console cable X1
- Power cord X 1
- M6 screw, cage nut & cup washer X8




The above package content is only for the single console models. It varies with options such as KVM, SDI, HDMI & DC power.

< 1.2 > Structure Diagram



< 1.2 > Dimension RM-X24


Front View




Rear View



 $\begin{array}{l} UNIT:mm\\ 1mm=0.03937\ inch \end{array}$



Top View




Model	Product Dimension	Packing Dimension	Net	Gross
	(W x D x H)	(W x D x H)	Weight	Weight
RM-X24	441.6 x 700 x 44 mm	595 x 910 x 140 mm	15.3 kg	19.5 kg
	17.4 x 27.6 x 1.73"	23.4 x 35.8 x 5.5"	33.7 lb	42.9 lb




The weight is only for the single console models. It varies with accessories & options such as KVM, SDI, HDMI & DC power.

< 1.3 > Installation - How to install Installation Slides




Step 1

■ Insert the left and right rear mounting brackets into the LCD console drawer.



Step 2

- Measure the depth of the front and rear mounting rails.
- Align each rear mounting bracket to a suitable length.



Step 3

Complete the installation

■ Fix the LCD console drawer into the rack.



M6 screw, cage nut & cup washer x 8 are provided.




■ Hold the handle and slide out the drawer.



■ Flip up the LCD to a suitable angle.




■ Operate the LCD console drawer.




Option - Right Side Open

■ Add R at the end of the model no. sample: RM-X24R

< 1.4 > Connection to USB Server via DVI-X cable



< 1.4 > Connection to external KVM via DVI-X cable





Caution: The LCD console drawer is hot-pluggable, but components of connected devices, such as the servers and KVM switch, may not be hot-pluggable. Plugging and unplugging cables while servers and KVM are powered on may cause irreversible damage to the servers, KVM and LCD console drawer. Before attempting to connect anything to the LCD console drawer, we suggest turning off the power to all devices. Apply power to connected devices again only after the LCD console drawer is receiving power. The company is not responsible for damage caused in this way.

< 2.1 > Product Specifications

LCD	Panel Size (diagonal)	24.1-inch Widescreen TFT color LCD
Panel	Display pixel (dots x lines)	1920 x 1200
	Brightness (typ.)	300
	Contrast Ratio (typ.)	1000:1
	Color	16.7 M
	Viewing Angle (L/R/U/D)	89/89/89
	Response Time (ms)	14
	Dot pitch (mm)	0.27
	Display Area (mm)	518.40H x 324.0V
	Surface treatment	Anti-glare, Hard-coating
	Surface hardness	3H
	Backlight Type	LED
	MTBF (hrs)	30,000

Video	Digital	HDMI	HDMI 1.3, CEA-861-D
Connectivity		DVI	DVI-D, TMDS single link
	Plug & Play	DVI	VESA EDID structure 1.3

Power	Power Supply	Range	Auto-sensing 100 to 240VAC, 50 / 60Hz
	Power Consumption	Screen ON	Max. 40W
	Fower Consumption with KVM integration	Power saving mode	Max. 5W
		Power button OFF	Max. 1W
		Screen ON	Max. 65W
		Power saving mode	Max. 30W

^{*}For details, please refer to our KVM rear kit user manuals


Regulatory	Safety	FCC & CE certified
	Environmental	RoHS2 & REACH compliant


Environmental	vironmental Operating	Temperature	0 to 55°C degree
Conditions		Humidity	20~90%, non-condensing
		Altitude	16,000 ft
	Storage / Non-operating	Temperature	-20 to 60°C degree
		Humidity	5~90%, non-condensing
		Altitude	40,000 ft
		Shock	10G acceleration (11ms duration)
		Vibration	5~500Hz 1G RMS random

Physical	Product (WxDxH)	441.6 x 700 x 44 mm
Specification		17.4 x 27.6 x 1.73 inch
	Packing (WxDxH)	595 x 910 x 140 mm
		23.4 x 35.8 x 5.5 inch
	Net Weight	15.3 kgs / 33.7 lbs
	Gross Weight	19.5 kgs / 42.9 lbs

Applicable	DVI-D Input	PC Signal	1920 x 1200 x 60Hz
Format			1360 x 768 x 60Hz
			1280 x 1024 x 60 / 75Hz
			1280 x 960 x 60Hz
			1280 x 768 x 60 / 75Hz
			1152 x 864 x 75Hz
			1024 x 768 x 60 / 70 / 75Hz
			848 x 480 x 60Hz
			800 x 600 x 60 / 72 / 75Hz
			720 x 400 x 70Hz
			640 x 480 x 60 / 72 / 75Hz
			640 x 400 x 70Hz
			640 x 350 x 70Hz
	HDMI Input	PC Signal	Same as VGA
		Video Signal	1080p : 60Hz
			720p : 50 / 60Hz
			480p : 60Hz
			576p : 50Hz
		Audio Signal	2ch Linear PCM (32 / 44.1 / 48 KHz)
		Speaker	Dual Stereo Speaker, 2 x 2W







tb keyboard integrated with trackball





Key force	55 ± 5g	
Travelling distance	3 ± 0.3mm	
Switch life	· 10 million life cycle time	
OS support	Windows / Linux / Unix / Mac OS	

tb


Supporting layouts





America	United States				
	United Kingdom	Germany	France	Spain	Norway
EMEA	Italy	Russia	Switzerland	Netherlands	Portugal
Asia	* China	Japan	Korea	Arabia	C * Turkey

< 2.2 > MAC Keyboard / Mouse Options














Supporting layouts

America




How to Use "MAC" Keyboard

Keyboard Features




Se

S keyboard integrated with touchpad












S keyboard integrated with touchpad / trackball


- Incorporates SUN keys, including Stop, Cut, Paste, Compose, Copy and Help
- 104 key notepad keyboard with full numerical pad and SUN function
- **USB** interface
- US layout only

How to Use "S" Keyboard



Num LED in Off mode

Key pad behaves as a SUN Solar system administration command mode



Num LED in Green mode

Key pad behaves as a normal key pad mode

Audio / Display Keys

* Please ask your supplier for full details



Audio: Mute Display: Degauss



Audio: Decrease volume Display: Decrease contrast



F12

Audio: Increase volume Display: Increase contrast

< 2.3 > On-screen Display Operation (OSD)



Membrane Switch	Function
٨	Turn the monitor on or off
	Display the OSD menu Act as an Enter key to select screen setting options
$\wedge $	Scroll through menu options and adjust the displayed control
D	Exit the OSD screen Go back to the previous on-screen sub-menu or main menu

Remark : All LED touch buttons in WHITE light.

The LED of **Power** touch button will flash continuously when there is no signal input.

1 All the LED touch buttons will automatically turn off after 10 minutes of idle status (except the **Power** (b)).

(2) Light up all membrane buttons, please press any button for 1 - 2 seconds (except the **Power** (b)).

Picture

Picture mode: Standard / Vivid / Soft / User mode to choose

Brightness: Adjust background black level of the screen image

Contrast: Adjust the difference between the image background

(black level) and the foreground (white level)


Hue: Adjust the screen hue value

Saturation: Adjust the saturation of the image color

Picture size: Adjust the image size

Color temp: Standard / Cool / Warm / User to choose

Noise reduce : Reduce the noise of the image Sharpness: Adjust the image from weak to sharp



2 PC


Auto adjust: Automatically adjust sizes, centers and fine tunes the

video signal to eliminate waviness and distortion.

Clock : Adjust the clock value

Phase : Adjust the phase value

H. Position : Align the screen image left or rightV. Position : Align the screen image up or down



3 Audio

Audio mode: Movie / Voice / Normal / Music mode to choose

Volume : Adjust the volume of sound


Bass : Set the value of bass sound

Treble : Set the value of treble sound

Balance: Set the balance value of treble and bass sound

Analog TV audio: Set the value of analog TV audio sound

Mute: Turn off the surrounding sound



4 MISC

Language: Select the language in which the OSD menu is

displayed - English


Sleep timer: Set the off time

PIP mode: Adjust picture in picture setting

PIP position : Enter into PIP position

PIP source : Enter into the Sub source and sound source System reset : Return the adjustment back to factory setting

Information: Select for Help




< 2.4 > How to Use Picture In Picture (PIP) / Picture By Picture (PBP)

< 2.4.1 > Picture in Picture (PIP)

Mode


Display the Sub screen in the Main screen. OSD Menu \to MISC \to PIP Mode \to Large / Small / OFF



Position

Adjust the position of the Sub screen (top left, bottom left, top right, bottom right)

OSD Menu \rightarrow MISC \rightarrow PIP Position \rightarrow top left / top right / bottom left / bottom right



Size

Adjust the size of the Sub screen (Large / Small) OSD Menu \to MISC \to PIP Mode \to Large / Small


Size of Sub screen

LCD Monitor	Large Sub screen	Small Sub screen
1920 x 1200	552 x 414	480 x 360
1920 x 1080	552 x 414	480 x 360
1440 x 900	414 x 310	360 x 270
1366 x 768	392 x 294	340 x 254
1280 x 1024	368 x 276	320 x 240

< 2.4.2 > Picture By Picture (PBP)

Mode

Display the Sub screen next to the Main screen. OSD Menu \rightarrow MISC \rightarrow PIP Mode \rightarrow PBP



Size

LCD Monitor	Main / Sub screen
1920 x 1200	955 x 716
1920 x 1080	955 x 716
1440 x 900	715 x 536
1366 x 768	678 x 508
1280 x 1024	635 x 476

< 2.4.3 > PIP / PBP Source

To select an input signal for PIP / PBP Sub screen.

 $\mathsf{OSD}\;\mathsf{Menu}\;\rightarrow\;\mathsf{MISC}\;\rightarrow\;\mathsf{PIP}\;\mathsf{Source}\;\rightarrow\;\mathsf{VGA}\;\;/\;\;\mathsf{S-Video}\;\;/\;\;\mathsf{Composite}\;\;/\;\;\mathsf{DVI}\;\;/\;\;\mathsf{HDMI}\;\;/\;\;\mathsf{SDI}\;\;/\;\;\mathsf{YPbPr}\;\;/\;\;\mathsf{TV}$

The PIP / PBP is operable in the following table :


Sub Main	VGA	S-Video	Composite	DVI-D	HDMI	SDI	YPbPr	TV
VGA	Х	0	0	0	0	0	0	0
S-Video	0	х	Х	0	0	0	О	х
Composite	0	х	Х	0	0	0	О	х
DVI	0	0	0	Х	Х	0	0	0
HDMI	0	0	0	Х	Х	0	0	0
SDI	0	О	0	0	0	Х	х	0
YPbPr	0	0	0	0	0	Х	х	0
TV	0	Х	Х	0	0	0	0	х

< 3.1 > Options : 3G / HD / SD-SDI input



Ôl^•æ⁄Q æ'^' SDI input is an ideal solution for the broadcast-grade video and high resolution CCTV market.

Designed for use with Cl^•cap(Q at ^ displays, a SDI input module can support up to 1080p @60Hz resolution without using additional space or power and it comes standard with a 2-year warranty.



^{***} For SDI option, casing depth will be changed from 700mm ($27.6 ^{\circ}$) to 750mm ($29.5 ^{\circ}$)

INPUT	3G-SDI IN	BNC x 1 / 0.8Vp-p (75 ohm)
	3G-SDI OUT	BNC x 1 / Active through, equalized & relocked
Standard Compliance	Video	SMPTE 425M / 274M / 296M / 125M ITU-R BT.656
	Audio	SMPTE 299M / 272M-C
Compatible Video Format	3G-SDI	1080p @60 / 50Hz, 4:2:2 1080p @30 / 25 / 24Hz, 4:4:4 1080i @60 / 50Hz, 4:4:4 720p @60 / 50Hz, 4:4:4
	HD-SDI	1080p @30 / 25 / 24Hz, 4:2:2 1080i @60 / 50Hz, 4:2:2 720p @60 / 50Hz, 4:2:2
	SD-SDI	480i @60Hz, 4:2:2
	ITU-R BT.656	576i @50Hz, 4:2:2

Compatible Audio Format	3G-SDI	48kHz, 16 / 20 / 24 bit, 2 CH, Synchronized Video
	HD-SDI	48kHz, 16 / 20 / 24 bit, 2 CH, Synchronized Video
	SD-SDI	48kHz, 16 / 20 / 24 bit, 2 CH, Synchronized / Asynchronized Video

Max. Transmission Distance	3G-SDI	150m at 2.97Gb/s
75 ohm coaxial cable	HD-SDI	250m at 1.485Gb/s
	SD-SDI	480m at 270Mb/s

< 3.2 > Options : FA!X24

- **HDMI** (HDMI 1.3, CEA-861-D)



- (1) For HDMI option, DVI-D input will be removed.
- (2) In some circumstances, if the user connects the LCD to PC via HDMI port for video and audio signals, the LCD may display incorrectly on a full screen. If so, please adjust the display card setting on display size to fix the issue.



< 3.3 > Options : DC Power



Model	24V	48V	125V	250V
Input rating				
Input voltage:	24-Volt	48-Volt	110-Volt	300-Volt
Input range:	18 ~ 36V	36 ~ 75V	66 ~ 160V	180 ~ 425V
Input current				
- No load	50 mA	50 mA	35 mA	10 mA
- Full load	4880 mA	2442 mA	749 mA	600 mA
Output rating				
Output voltage:	12-Volt	12-Volt	12-Volt	12-Volt
Output current:	4.16A	4.16A	6.25A	12.5A
Efficiency	85%	85%	91%	86%

DC power



- *** For DC power option :
 - (1) If the unit with LCD, earthing may be required
 - (2) DC option excludes AC power adapter and power cord.
 - (3) Casing depth will be extended from 700mm (27.6") to 750mm (29.5")

The company reserves the right to modify product specifications without prior notice and assumes no responsibility for any error which may appear in this publication.	
All brand names, logo and registered trademarks are properties of their respective owners.	